

## Thermoplastic Elastomers for Consumer Products

Monprene® TPEs add value to consumer products by improving product performance, aesthetics and tactile appeal. Overmolding Monprene onto a rigid plastic handle provides a soft grip that won't slip, even when wet. Monprene grips enhance the ergonomics of common household appliances and handheld devices as does anti-skid and anti-vibration parts made from Monprene TPEs.

### Monprene CP-10100 Series and CP-11100 Series

- Standard grades developed specifically for consumer products
- Wide hardness range: 40 to 90 Shore A
- Available in low and high density
- Light, natural color for superior colorability
- Suitable for skin contact
- Resistant to household chemicals and cosmetics
- Broad thermal performance
- High flow for improved moldability
- Excellent adhesion to polyolefins
- Recommended for injection molding, insert, and 2K molding



### Versatility meets functionality with Monprene TPEs:

Monprene is soft enough to provide a comfort grip on a toothbrush yet tough enough to withstand hours of chewing when molded into a dog toy. Monprene can be customized to suit the application which allows OEMs and processors more design flexibility.

- Personal Care: grips for toothbrushes and razors
- Writing Instruments: grips and erasers
- Sporting Goods: swim fins, grips, cushioning
- Hand-held Appliances and Tools: grips, buttons, anti-skid pads
- Pet Care: dog toys, groomer grips and accessories
- Toys

### Monprene CP-10100 Series for Consumer Products - Low Density

Property	Test Method and Condition	Units	CP-10140	CP-10150	CP-10160	CP-10170	CP-10180	CP-10190
Hardness	ISO 868 5 sec del	Shore A	40	50	60	70	80	90
Specific Gravity	ISO 1183	-----	0.89	0.89	0.89	0.89	0.89	0.89
Tensile Stress (break)	ISO 37 across flow	psi (MPa)	960 (6.6)	1060 (7.3)	(1510) 10.4	(1800) 12.4	2030 (14)	2470 (17)
Tensile Elongation (Break)	ISO 37 across flow	%	920	870	880	885	840	810
Tensile Stress (100 % Strain)	ISO 37 across flow	psi (MPa)	130 (0.9)	170 (1.2)	240 (1.7)	320 (2.2)	470 (3.3)	710 (4.9)
Compression Set	ISO 815 Type A 22 hrs at 70°C	%	28	30	35	37	44	47
Tear Strength	ISO 34-B flow direction	kN/m	22	27	32	39	50	62
Viscosity	ASTM D3835 206 1/s, 200°C	Pa.s	209	222	233	240	260	268

### Monprene CP-11100 Series for Consumer Products - High Density

Property	Test Method and Condition	Units	CP-11140	CP-11150	CP-11160	CP-11170	CP-11180	CP-11190
Hardness	ISO 868 5 sec del	Shore A	40	50	60	70	80	90
Specific Gravity	ISO 1183	-----	1.15	1.15	1.15	1.15	1.15	1.15
Tensile Stress (break)	ISO 37 across flow	psi (MPa)	95 (0.7)	145 (1.0)	210 (1.4)	290 (2.0)	450 (3.1)	750 (5.2)
Tensile Elongation (Break)	ISO 37 across flow	%	950	900	885	835	790	725
Tensile Stress (100 % Strain)	ISO 37 across flow	psi (MPa)	990 (6.8)	1250 (8.6)	1480 (10.4)	1580 (10.9)	1710 (11.8)	1945 (13.4)
Compression Set	ISO 815 Type A 22 hrs at 70°C	%	26	28	33	38	49	57
Tear Strength	ISO 34-B flow direction	kN/m	18	22	27	31	39	47
Viscosity	ASTM D3835 206 1/s, 200°C	Pa.s	200	207	196	194	218	248

- PVC, latex, BPA, and phthalate free
- RoHS, CONEG, and Prop 65 compliant
- REACH SVHC compliant



**Americas**  
505 Central Avenue  
Pawtucket, RI 02861  
USA  
401-725-8000  
800-556-3862

**Europe**  
Mijnweg 1  
6167AC Geleen  
Netherlands  
31(0) 46 7020950

**Asia**  
41 Shipyard Road  
Singapore  
(011) 65-6265-2544

The information and recommendations contained in this bulletin are, to the best of our knowledge, accurate and reliable but no guarantee of their accuracy is made. All products are sold upon condition that purchasers shall make their own tests to determine the suitability of such products for their particular purposes and uses and purchaser assumes all risks and liability for the results of use of the products, including use in accordance with seller's recommendations. Nothing in this bulletin constitutes permission or a recommendation to practice or use any invention covered by any patent owned by this company or by others. There is no warranty of merchantability and there are no other warranties for the products described. For detailed Product Stewardship information, please contact us. Any product of Teknor Apex, including product names, shall not be used or tested in any medical or food contact application without the prior written acknowledgment of Teknor Apex as to the intended use. Please note that some products may not be available in one or more countries.